

71609

Ultra Hygiene Squeegee, 600 mm, , Black



This ultra hygienic squeegee has a very soft and effective rubber lip, which ensures effective cleaning of floors and other surfaces. The rubber lip is angled to facilitate cleaning close to walls and around equipment without any problems. The squeegee's splash guard ensures that the liquid is not splashed onto the dried surface.

Technical Data

Item Number	71609
Material	Polypropylene TPE Rubber
Suitable for Food Contact (EU 1935/2004), DoC ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	15 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	480 Pcs
Quantity Per Layer (Pallet)	60 Pcs.
Box Length	615 mm
Box Width	295 mm
Box Height	210 mm
Length	600 mm
Width	80 mm
Height	95 mm
Gross Weight	0,39 kg
Net Weight	0,36 kg
Cubik metre	0,0033 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	50 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705020716096
GTIN-14 Number (Box quantity)	15705020716093
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact