

Product Data Sheet

CV 38/2 & CV 48/2

Professional Upright Vacuum Cleaners.

Tough, high performance upright vacuum cleaners for professional applications, featuring individual brush and suction motors for superb cleaning performance and reliability. With fast, dust-free bag change, a range of tools stored conveniently on the machine and a cleaning width of 38cm or 48cm the CV 38/2 and 48/2 clean quickly and thoroughly with the minimum of effort.



Features and Benefits:

- Easily adjustable brush height with warning light
- Accessory tools stored on the back of the machine for quick access
- Patented removal system for fast, dust-free replacement of filter bags
- Tear-resistant fleece-filter bag
- High quality, low noise suction hose
- Quick-release handle adjustment to suit all operators
- Low nose height for easy access under objects
- Low weight enabling fatigue-free operation



Range Comparison

Kärcher Vacuum Cleaners



Accessories

Standard Accessories



Roller Brush Black
6.906-643 (CV 38/2)
4.762-489 (CV 48/2)



Crevice Tool
6.906-240



Upholstery Tool
6.900-233



Fleece Filter Bag
6.904-305

Optional Accessories



HEPA-Exhaust Air Filter Cassette
6.414-760



Fabric Filter Bag
6.904-301



Round Brush
6.903-862

Technical Specification

Working width, brush (mm)	380 / 480*
Motor rating (W)	1200
Brush motor rating (W)	150
Air flow rate (l/s)	48
Vacuum (Kpa)	25
Container Capacity (l)	5.5
Power cable (m)	12
Operating noise (dB(A))	66
Weight (kg)	9.5
Dimensions (L x W x H) (mm)	1215 x 390 x 350
Part Number	1.033-316 / 1.057-311*

* CV 48/2



Tel: 01295 752 082

Kärcher (UK) Ltd, Beaumont Road, Banbury, Oxon OX16 1TB
info@kärcher.co.uk www.kärcher.co.uk