

B1004 - K-Step/K-Speed/K-Move/K-Start S1P HRO SRC

Collection: Kaptiv

Upper: Breathable Fabric

Insole: Wire Lace System

Lining: SmellStop Antiodor and Antibacterial*

Midsole: Fresh'n Flex

Toecap: Aluminium

Sole: Double-Density PU/HRO Rubber i-daptive® Technology

Outer Carton: 10



Kaptiv

The first safety footwear range with stability control, designed to offer incredible dynamic comfort.

Base

Comfort is what has inspired Base Protection since its first day of activity. The company produces safety footwear, combining technology and functional requirements, to respond to professional and more demanding clients.

Standards

EN ISO 20345: 2011 S1P (HRO SRC)

Features

- Anti-static footwear
- 200 joules resistant toe-cap
- Puncture resistant sole
- Shock absorption in the heel region
- Heat resistant 1 minute up to 300°C
- Hydrocarbons resistant
- Men's width
- Women's width
- Orthopaedic made to measure footbed, complying with european norms DGUV112-191

B1004 - K-Step/K-Speed/K-Move/K-Start S1P HRO SRC**Commodity Code: 6404199000****Test House**

A.N.C.I. Servizi S.R.L (CIMAC) (Notified Body No.: NB: 0465)

Via Alberto Riva Villasanta, 3

, Italy

Cert No: N° F-113-05202-22

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
B1004BKY36	Black/Yellow	67.0	41.0	36.0	1.1700	0.0989	8054633494363	
B1004BKY37	Black/Yellow	67.0	41.0	36.0	1.1790	0.0989	8054633494370	
B1004BKY38	Black/Yellow	67.0	41.0	36.0	1.2020	0.0989	8054633494387	
B1004BKY39	Black/Yellow	67.0	41.0	36.0	1.2530	0.0989	8054633493380	
B1004BKY40	Black/Yellow	67.0	41.0	36.0	1.2860	0.0989	8054633493397	
B1004BKY41	Black/Yellow	67.0	41.0	36.0	1.3390	0.0989	8054633493403	
B1004BKY42	Black/Yellow	67.0	41.0	36.0	1.3630	0.0989	8054633493410	
B1004BKY43	Black/Yellow	67.0	41.0	36.0	1.4260	0.0989	8054633493427	
B1004BKY44	Black/Yellow	67.0	41.0	36.0	1.4610	0.0989	8054633493434	
B1004BKY45	Black/Yellow	67.0	41.0	36.0	1.5040	0.0989	8054633493441	
B1004BKY46	Black/Yellow	67.0	41.0	36.0	1.5350	0.0989	8054633493458	
B1004BKY47	Black/Yellow	67.0	41.0	36.0	1.6180	0.0989	8054633493465	
B1004BKY48	Black/Yellow	67.0	41.0	36.0	1.6290	0.0989	8054633493472	