

Features

- Needle-nose pliers with long serrated jaws, rounded on the outside, ideal for gripping components in tight spaces without damaging them.
- Steel thickness 3 mm.
- Pliers are equipped with a return spring designed to have a constant force, thus reducing operator effort.
- Ergonomic anti-slip bicomponent handle for a safe, light and comfortable grip
- Anti-reflection phosphating surface treatment.
- ESD safe version.
- Laser marking.
- Made in Italy.

RS PRO ESD long needle-nose pliers. Medium head.

RS Stock No.: (0429689)



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Made in Italy with high carbon steel and undergo a controlled atmosphere heat treatment.
- This plier is ideal for different applications in microelectronics, jewellery making, laboratory, watch making and repairs, DIY.
- The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.
- The tools are joined with grounded holes and surfaces, thereby allowing precise movements.
- The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator even when used constantly for many hours.
- ESD-safe version.

General Specifications

Plier Type	Long needle-nose pliers. Medium head.
Tip Style	Pointed, rounded outside
Serrated internally	YES
Material	High carbon steel
ESD Safe	YES. Standard IEC 61340-5-1

Mechanical Specifications

Steel thickness	3 mm
Hardness	Hrc 48-50
Length of the head	32 mm
Overall Length	160 mm
Weight	78 g

