

26" T Model LCD MFM

Artistry isn't something that can be measured. At SAMSUNG, we believe that artistry is the result of a delicate balance between high-end design and cutting-edge technology. We're inspired by the world around us and want to create products that are both functional and exude beauty. Introducing the T260HD from SAMSUNG. Beautiful, inside and out.



full HD 1080p



enhanced connectivity



1080p Full HD technology means you are watching the highest resolution images available today. Nearly twice the resolution of regular HDTV, you will experience an astoundingly vivid and realistic picture and incredible image. More pixels mean higher definition and that means more detail than ever before with 1920 x 1080 Full HD technology, giving you the most lifelike images and astounding clarity no matter how fast the action.

A comprehensive array of connection options allows SAMSUNG LCD monitors to be connected to external A / V devices. The incorporation of Component, D-Sub, DVI-D, USB 2.0 and HDMI connectors makes connection convenient and complete.

invisible speaker system



At first glance you might think that we forgot to include the speakers, but with our innovative invisible Speaker System, they are neatly hidden within the body of the monitor in order to maintain the clean, fluid lines of the exterior. For an even more enhanced surround sound experience, the T series monitor includes SRS Tru Surround XT™, a patented audio technology specifically designed for a two-speaker output system. Plus, our parametric EQ technology enables our speakers to reproduce deeper and clearer sound without distortion over the entire range of frequencies.

2 HDMI



Now fully equipped with two HDMI (High Definition Multimedia Interface) connections. Connect HD digital devices such as AC devices, game consoles, digital cameras and camcorders into the two HDMI ports to make the most of your HD experience.

embedded DTV tuner



With the built-in Digital Television (DTV) tuner, the T series immediately widens your entertainment world. Unlike many monitors, the T series can decode and display free, over-the-air digital TV broadcasts without buying any additional equipment. So now your PC monitor enables you to watch your favourite TV programmes while working on your PC. Now that's multi-tasking!

low power consumption



Power consumption is always a concern when it comes to home electronics. The T series monitor from SAMSUNG consumes only 65-70W in operation mode. Compared to other monitors, that's a reduction of almost 30W. And with the unique SoftPower Off function, the monitor consumes a mere 0.3W when on standby. So with the T series, you can work productively at home without worrying about driving up your energy bill.

Screen Size	26" Widescreen
Resolution	1920 x 1200
Brightness	300cd/m ²
Contrast Ratio	DC 10000:1 (1000:1)
Viewing Angle (Horizontal/Vertical)	170/150