

375040162

Stainless steel industrial enclosure IGGN A4 500 x 400 x 161 mm

Stainless steel industrial enclosure IGGN A4 500 x 400 x 161 mm

Drawing 3D Data

Technical data

Height	500 mm
Width	400 mm
Depth	161 mm
Material	Stainless Steel
Material quality	1.4404/316L
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-60 °C
temperature max.	175 °C
Seal material	VMQ-(silicone)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Smoke gas concentration	HL 3
Other versions on request	EMV
Approvals	LR (Lloyd's Register), UL (508A)

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tarif number	85369095
Weight	7.69 kg
GTIN	4057624608071


ETIM classification

ETIM 8	EC000058


ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de


Accessories



100110490
Mounting plate for 37.504016



100614400
DIN rail 35/7,5 for 37.504016




100620250
Earth rail for 37.503016




100681250
Protective conductor busbar for 34.50xxx /xx.0053xx



370000020
Stainless Steel External hinge




370100040
Flange size 4 - 130x360x3



370100050
Flange size 5 - 130x480x3



371050000
Stainless steel external mounting brackets



379900010
Mounting set for Stainless-steel enclosures