

3380879

WCS3900

CCD BARCODE SCANNER



Big Business Tools. Small Business Attitude.

The Wasp WCS 3900 series scanners are the most popular bar code scanning devices in our product line. Manufactured from light weight ABS plastic for durability, and our exclusive ergonomic design for comfort and ease of use, make the WCS 3900 and WCS 3905 bar code scanners the best in their class. For fast connection, the WCS 3900 simply plugs between your keyboard and PC, or if you prefer USB, the WCS 3905 is the scanner for you. Both scanners send data to your active application as if you typed it from your keyboard. Designed for retail, point of sale, or any repetitive application where time and accuracy are important factors in making your business succeed. Optional stand available for hands free scanning applications!

WASP WCS3900 FEATURES

- ▶ One touch scanning
- ▶ Ergonomic design
- ▶ Light weight
- ▶ Durable
- ▶ Hands free scanning
- ▶ Economical
- ▶ Quick connect

BENEFITS

- ▶ Simply aim the scanner over the barcode and pull the trigger, it's that easy
- ▶ Comfortable form, fit, and feel. Perfect for repetitive applications
- ▶ Less fatigue
- ▶ Manufactured from high quality ABS plastic for strength
- ▶ Use with optional stand for hands free scanning. Ideal for retail & point of sale applications
- ▶ Best scanner for the price
- ▶ Easily connect via PS2 or USB cable

WASP WCS3900 COMMON USES

- | | |
|--------------------|------------------------|
| ▶ Retail | ▶ Medical |
| ▶ Point of Sale | ▶ Legal |
| ▶ Office | ▶ Government |
| ▶ Light Industrial | ▶ Marketing |
| ▶ Libraries | ▶ Warehouse Management |

3380879

WCS3900

CCD BARCODE SCANNER



Big Business Tools. Small Business Attitude.

■ SPECIFICATIONS

OPTICAL FEATURES	Light source: 660 nm red visible LED Sensor: 2088 linear imager Scanning width: 3.25" (80mm) Depth of field: Contact to 1" / 0 to 2.5 cm Scan Rate: 45 scans / second Decode rate: 100 scans / second
ELECTRICAL CHARACTERISTICS	Operating voltage: +5 VDC ±5% Current consumption: Decoded: Standby < 30 mA / Working < 95 mA
MECHANICAL CHARACTERISTICS	Dimensions: 7.40" L x 3.62" W x 1.06" H7 lbs (3 kg) Net weight: 125 g (without cable) Cable: 6 foot Housing: ABS
ENVIRONMENT CHARACTERISTICS	Operating temperature: 0°C to 50°C Storage temperature: -20°C to 60°C Relative humidity: 20% TO 80% non-condensing Safety certification: Conforms FCC Class A and CE requirements
1D (LINEAR) SYMBOLOGIES READ	Codabar, Code 3 of 9 (Code 39), Code 3 of 9 Full ASCII, Code 11, Code 32, Code 93, Code 128 (including UCC/EAN 128), EAN/JAN-8 (plus supplements), EAN/JAN-13 (plus supplements), Industrial 2 of 5 (25), Interleaved 2 of 5, ISBN, Matrix 25, MSI Plessey, UPC-A (plus supplements), UPC-E (plus supplements), China Post Code, RSS14, Telepen
PART NUMBERS	WCS3905 CCD Barcode Scanner with USB cable: 633808502935 WCS3900 CCD Barcode Scanner with PS2 cable: 633808501051 WCS3900 CCD Barcode Scanner Stand: 633808091057