



PRODUCT-DETAILS

TY25M-7

CABLE TIE 50LB 7IN PURPLE NYLON



概要信息	
产品型号	TY25M-7
产品ID	7TAG009270R0017
欧洲商品编号(EAN)	5414363062608
目录说明	CABLE TIE 50LB 7IN PURPLE NYLON
详细描述	High Performance Cable Tie for Indoor applications, Purple Color Nylon 6.6, Length of 186mm (7.3 Inches) for Bundle Diameter up to 48mm (1.89 Inches), Width of 4.9mm (0.19 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Military Specified (MIL-SPEC MS3367-1-7), Bulk Pack
订货信息	
欧洲商品编号(EAN)	5414363062608
UPC	786210844909
原产地	United States (US)
销售度量单位	件

尺寸		
产品净宽	0.19 in	4.9 mm
产品净深	7.2 in	183 mm

包装信息		
1级包装单元	1000 EA	
1级包装宽度	0 mm	0 in
1级包装高度	0 mm	0 in
1级包装长度	0 mm	0 in
2级包装单元	10000 EA	
2级包装宽度	370.84 mm	14.6 in
2级包装高度	350.52 mm	13.8 in
2级包装长度	495.3 mm	19.5 in

UL/CSA适用的技术参数		
可燃性符合UL94标准	V-2	

其他信息		
品牌/标签	Ty-Rap	
Bundle Diameter	0.12 to 1.89 in	3 to 48 mm
颜色	Purple	
有效期	19680313	
Lock Type	Stainless Steel Barb	
材料	Nylon/Polyamide 6.6	
产品	Other: Other	
产品应用类型	High Performance	
特殊功能	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.	
标准	UL E49405	
Tensile Strength	50 lb	222 N
Thickness	0.05 in	1.3 mm

认证及声明（文件编码）		
数据手册，技术资料	TDS000518	
符合性声明 - CE	9AKK107492A9841	

分类		
----	--	--

ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
ETIM 9	EC000046 - Cable tie
UNSPSC	39121703
WEEE 类别	Product Not in WEEE Scope
IDEA 粒度分类代码 (IGCC)	5034 >> Cable ties

分类

低压产品及系统 → 安装产品 → 电缆管理和连接 → Cable Ties

