

A715 - Grip 15 Nitrile Impact Glove

Collection: Impact protection

Range: Hand Protection

Materials: Nylon, Elastic, Elastane, Carbon Fibre, TPR

Dipping:

Outer Carton: 72

Product information

Experience the ultimate in safety and performance with our advanced glove, expertly engineered to deliver unparalleled impact protection and extraordinary versatility. Specifically designed for low-energy impact protection, it safeguards against demanding tasks. Compatible with most touchscreen devices, this glove allows for seamless interaction without the need for removal. Made with an ESD liner to reduce the risk of electrostatic discharge in sensitive environments.

Impact protection

Hand injury is one of the most common and frequent complaints in the workplace. This collection of gloves provides vital protection against impact to the hand from multiple hazards.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 5

EN 388: 2016 + A1: 2018 (4131XP)

ANSI/ISEA 105: 2016 CUT Level (A1)

ANSI/ISEA 105: 2016 ABRASION Level (4)

ANSI/ISEA 105: 2016 PUNCTURE Level (2)

ANSI/ISEA 138: 2019 (LEVEL 2)



Features

- For low-energy impact protection
- Nitrile foam coating for excellent grip in wet and dry conditions
- This glove can be used with most mobile touchscreen devices
- 15 gauge liner provides the best balance of dexterity and durability
- Retail tag which aids presentation for retail sales
- Suitable for use in ESD environments
- New style
- CE certified



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

A715 - Grip 15 Nitrile Impact Glove

Commodity Code: 6116102091

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777/26090-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
A715K8RS	Black	58.0	38.0	28.0	0.1160	0.0617	5036108414154	15036108899675
A715K8RM	Black	58.0	38.0	28.0	0.1300	0.0617	5036108414147	15036108899668
A715K8RL	Black	58.0	38.0	28.0	0.1350	0.0617	5036108414130	15036108899651
A715K8RXL	Black	58.0	38.0	28.0	0.1470	0.0617	5036108414161	15036108899682
A715K8RXXL	Black	58.0	38.0	28.0	0.1520	0.0617	5036108414178	15036108899699