

## Han 16HP Direct/EMC-PFT-Housing-SE-M40



Image is for illustration purposes only. Please refer to product description.

Part number	19 39 816 1133
Specification	Han 16HP Direct/EMC-PFT-Housing-SE-M40
HARTING eCatalogue	<a href="https://harting.com/19398161133">https://harting.com/19398161133</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han <sup>®</sup> HP Direct EMC
Type of hood/housing	Panel feed through housing

### Version

Size	16 B
Version	Side entry
Number of cable entries	1
Cable entry	1x M40
Locking type	Screw locking

### Technical characteristics

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP66 IP68 IP69 / IPX9K acc. to ISO 20653

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Electrical conductive
Colour (hood/housing)	Unpainted
Material (seal)	NBR



Pushing Performance  
Since 1945

## Material properties

Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE

## Commercial data

Packaging size	1
Net weight	627 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140183179
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466