



ST2-520-S-YT

E1518140

STAINLESS STEEL CABLE TIE, 520x4.6mm SS316



Product Properties:

Detectable	No
Min. tensile strength	667 N
Model	Without tothing
Material quality	Stainless steel 316 (V4A)
Operating temperature	-80-538 °C
Mounting temperature	-80-538 °C
Band closure	Ball latch
UV-stable acc. ASTM D6779	Yes
Transparent	No
Fluorescent	No
Solvable fastener	No
Text strip	None
Type of fastening	None
Colour	Stainless steel
Surface protection	Untreated
Material	Metal
Halogen free	Yes
Max. tensile force	667 N
Inflammability class of insulation material according to with UL94	Other

Dimensions:

Bundle diameter	20-150 mm
-----------------	-----------

MOQ	100 .
Unit	pcs
Length belt/tape/tie	520 mm
Tie thickness	0.25 mm
Band width	4.6 mm
Max. bundle diameter	158 mm
Max. tensile force	667 N

Approvals:

MIL approval	No
VG approval	No
UL approval	Yes
Inflammability class of insulation material according to with UL94	Other

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Extended Minerals	N/A, contains no extended minerals
Iron and Steel Sanction	Compliance
PFAS	No PFAS
REACH	No SVHC (Latest. 21 Jan 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000046 - Cable tie
ETIM-Release	10.0
Trademark	NEMIQ
Product Group	Cable ties, steel
Search Description	STÅLBUNTBAND, ROSTFRITT, 520X4.6MM
Alternative SKU	ST2-520-S-YT
E-no	E1518140

Logistic information:

Barcode	733117639014
Country of origin	IN
E-no	E1518140
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	100 .
Stock code	ST2-520-S-YT

Taric code	73269098
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.