

Main

Range	Odace
Product or component type	Reading lamp
Device application	Reading USB charger
Device mounting	Flush
Device presentation	Mechanism with fixing frame
Switch function	Dimmer
Switch application	On/off switching
Colour tint	Anthracite
Market segment	Hotel

Complementary

Type of USB power supply	USB type A
Actuator	Push-button
Rated lamp wattage	2 W
[Ue] rated operational voltage	240 V
Bulb base	Integral LED
Bulb type	LED
Control type	Touch type
Luminous flux	100 lm
Integrated connection type	USB port
Output current	2.1 A
Fixing mode	Screws
Shape of screw head	Pozidriv No 1
Clamping connection capacity	2.5 mm ² for flexible cable(s) 2.5 mm ² for rigid cable(s)
Height	71 mm
Width	71 mm
Depth	45 mm

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins