

ALPHA

3370PIR160P63

EAN 4031582423648

Swivel castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, wheel axle with nut, plate fitting. Wheel centre made of Polypropylene, Tread: solid rubber, grey non-marking, roller bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	160 mm
Wheel width	40 mm
Size of Plate	137 x 105 mm
Plate hole centres	105 x 80/77 mm
Plate hole	11 mm
Offset	57.5 mm
Swivel Interference	275 mm
Overall height	200 mm
Temperature	- 20 / + 60 °C
Standard	EN_12532
Load capacity	135 kg
Load capacity (static)	270 kg

Advantages at a glance

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○