

LED lamp with motion detector, magnet mounting, 100-240 V AC/DC 50/60 Hz



Model				
product brand name		SIVACON		
product designation		LED light		
design of the product		BW with magnetic fixing		
type of light source		LED not replaceable		
General technical data				
consumed active power of the light source		5 W		
type of voltage of the operating voltage		AC		
Protection class				
protection class IP		IP20		
Product details				
product component				
• ON/OFF switch	No			
• light sensor	Yes			
• socket outlet	No			
product feature magnetic		Yes		
Connections				
type of electrical connection for through-wiring		Plug-in connection		
Mechanical Design				
height		34 mm		
width		32 mm		
depth		34 mm		
length		351 mm		
fastening method		magnetic fixing		
net weight		0.2 kg		
material		plastic		
Approvals Certificates				
General Product Approval		other	Dangerous goods	Environment



[Confirmation](#)

[Transport Information](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR2200-0A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR2200-0A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR2200-0A

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/15/2025 

