



Main

Commercial Status	Commercialised
Range of product	Cable ends
Product or component type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of packing	String of bags
Quantity per set	10 sets of 100
Cable cross section	0.01 in ² (4 mm ²)

Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Colour	Orange
Bezel material	Halogen-free plastic
Tube material	Copper conforming to ISO 1337
Number of cables	1
AWG gauge	12
Bezel size	Ø 5.5 mm
Tube diameter	0.13 in (3.3 mm)
Length	0.68 in (17.3 mm)
Tube length	0.39 in (9.8 mm)
CAD overall width	0.24 in (6 mm)
CAD overall height	0.24 in (6 mm)
CAD overall depth	0.67 in (17 mm)
Product weight	0.66 lb(US) (0.3 kg)

Environment

Product certifications	UL
Ambient air temperature for operation	-4...221 °F (-20...105 °C)

Ordering and shipping details

Category	22621 - IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	00785901223221
Nbr. of units in pkg.	1000
Package weight(Lbs)	0.01
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	FR

Contractual warranty

Period	18 months
--------	-----------