

DWE4257KT-QS

Meuleuse 125 mm 1500W - vitesse variable



5035048659786

Product Description:

Disc Ø (mm): 125 Power : 1500W Regim empty (rpm) 0-2800/10000/variable
Spindle Thread: M14/Vibration Level (m/s²): 8.35/Switch: Slide/Perform & Protect/Clutch



Product features and benefits:

- Variable electronic speed to adapt the speed to different materials
- Gearbox with low profile so that it can work in limited spaces
- Motor protected against abrasion of dust particles, for greater longevity
- New disc clamping system, prevents blockage
- The high-quality dust extraction system provides visibility and ensures a clean working space
- The large double rear gauge, with its sliding parts, ensures good support for large cross-section parts, in single or combined miter cuts
- Electromechanical torque reduces the transmitted anti-reverse effect
- The tool remains inactivated during power-up even if the switch is left in the locked position, for greater

-
-

Safety Overload protection, prevents overheating by shutting down the

- motor to allow cooling of the mechanism
- Dust ejection system, removes the majority of debris,
- protects the motor from particles
- Anti-vibration side handle, improves user comfort
- Quickly adjustable, tool-free guard
- Inductor with connecting wires directly from the winding, for better tool life
- Self-adjusting brushes for longer motor life

-

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Protective guard Ø125 mm (x1)
- Multi-position side handle (x1)
- Indoor/Outdoor Flange (x1)
- 125 mm diamond blade (x1)
- TSTAK Kitbox (x1)

Specifications techniques :

- Power supply: 1500
- In
- Diameter: 125 mm
- [Imperial] Disc: 5 in
- Diameter: 125 mm
- [Imperial] Diameter: 5 in
- - Disc diameter: 125 mm