

Product datasheet

Specifications



trip unit TM80G for ComPacT NSX
100/160/250 circuit breakers,
thermal magnetic, rating 80 A, 3
poles 3d

C103MG080

EAN Code: 3606482000520

Main

Range	ComPacT
Range of product	ComPacT NSX100...250 ComPacT NSX100...250 DC
Product or component type	Trip unit
Trip unit name	TM-G
Trip unit technology	Thermal-magnetic
Range compatibility	ComPacT NSX100 ComPacT NSX160 ComPacT NSX100 DC
Device application	Generator
Poles description	3P
Protected poles description	3D
Trip unit protection functions	LI
Protection type	L : for overload protection (thermal) I : for short-circuit protection (magnetic)
Trip unit rating	80 A at 40 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz 750 V DC
Network type	AC DC
Network frequency	50/60 Hz
Circuit breaker mounting mode	Fixed

Complementary

Long-time pick-up adjustment type Ir (thermal protection)	Adjustable
[Ir] long-time protection pick-up adjustment range	0.7...1 x In
Long-time protection delay adjustment type tr	Fixed
[tr] long-time protection delay adjustment range	120...400 s at 1.5 x In
Instantaneous protection pick-up adjustment type Ii	Fixed
[Ii] instantaneous protection pick-up adjustment range	200 A
Earth-leakage protection	Without

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN/IEC 60947-2
Electrical shock protection class	Class II
Pollution degree	3 conforming to IEC 60947-1
IP degree of protection	IP40 conforming to IEC 60529
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.000 cm
Package 1 Width	10.000 cm
Package 1 Length	12.000 cm
Package 1 Weight	608.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	32
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	19.876 kg
Unit Type of Package 3	P12
Number of Units in Package 3	256
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	171.008 kg

Logistical informations

Country of origin	CN
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	103
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Recycled metal content at CR level	0
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	Cc480bde-e4f7-4f0c-ae59-ff70fd9f5b22
REACH Regulation	REACH Declaration
Halogen content performance	Product contains halogen above thresholds

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins