

suffixes.

- 5A, 277V ac; 10A 250V ac; 16A, 125V ac; 3/4HP 125-250V ac; R---, LR---
- 6A, 125V ac, 3A, 250V ac, TGC60 to TCG65 incl., TCG6T0 to TGC6T5, TIGAR6A to TIGAR6F, TIGAR6ACJ to TIGAR6FCJ.
- 6A, 125V, 3A, 250V, 110, 110-M, -B, -BM, -S, -SM, -P, -PM-OFF, -PM-ON, -BP, -BPM-OFF, -BPM-ON, -SP, -SPM-OFF, -SPM-ON, 111-16, -16M, -16P, -16-PM-OFF, -16-PM-ON, S111, 901 to 904 incl.
- 6A, 125V ac, 3A, 250V ac, 1/4 hp, 125-250V ac, RA---, RB---, RC---, LRA---, RRG---; may have additional suffixes.
- 6A, 125V ac, 3A, 250V ac, 1/4 hp, 120-240V ac, 2FA61, 2FA63 to 2FA65, 6FA61, 6FA63, 6FA64, 6FA66, 6FA67, 6FA68, 2FB61, 2FB63, 2FB64, 2FC61, 2FC63, 2FC64, 6FB61, 6FB63, 6FB64, 6FC61, 6FC63, 6FC64, 6FC66, 6FC67, 6FC68, LA463, LA464, LA46A, LB643, LB464, LB46A, LC463, LC464, LC46A.
- 6A, 125V ac, 3A, 250V ac, 1/4 hp, 125-250V ac, TIGA6A to TIGA6F, TIGA6L, TIGA6M, TIGA6Q to TIGA6T, TIGA60 to TIGA65.
- 6A, 125V ac, 3A, 250V ac, 3/4A, 125V, Series P26 and P27 with suffix letters A to F or L to T.
- 6A, 125V ac, 3A, 250V ac, 5A, 12V, 3/4A, 125V, Series P265 with Suffixes L to T.
- 6A, 125V ac, 3A, 277V ac, Series P267 with Suffixes A to F, L to T.
- 6A, 125V ac, 3A, 250V ac, 1/4 hp, 125-250V ac, 2G061, 2G063, 2G064, 2GA60 to 2GA65, 2GB60 to 2GB65, 2GC60 to 2GC65, DA..., DB..., DC..., TIGA61, TIGB60 to TIGB65, TIGC6L, TIGC6M, TIGC6Q to TIGC6T, TIGCD6L, TIGCD6M, TIGCD6Q to TIGCD6T, TILA60 to TILA65, TILA6A to TILA6F, TILA6L, TILA6M, TILA6Q to TILA6T, TILB60 to TILB65, TILB6A to TILB6F, TILC60 to TILC65, TILC6A to TILC6F, TILC6L, TILC6M, TILC6Q to TILC6T, LTILA6L, 6M, 6Q to 6T, LTILA60 to LTILA65, LTILB60 to LTILB65, LTILC60 to LTILC65, LTILC6L, LTILC6M, LTILC6Q to LTILC6T, LTIGKJ60 to LTIGKJ65, TIGX60 to TIGX65.
- 6A, 125V ac, 3A, 250V ac, 6A, 28V dc, Keylock Type, Series K (standard version).
- 6A, 125V ac (tungsten), 3A, 250V ac, DA..., DB..., DC...
- 8A, 125V ac, 4A, 250V ac, NPA380, NPA381, NPA385, NPB380, NPB381, NPB385.
- ● 2A, 250V ac (non-ind); 5A, 125V ac (non-ind), or 4A, 250V ac; 8A, 125V ac, may have 1/4 hp, 125-250V ac or 8A, 14V dc, Series 6 with suffixes.
- 11A, 125V ac (non-inductive).
- 8A, 125V, 4A, 250V, 164, 164-A, -B.
- 8A, 125V ac (non-inductive), 4A, 250V ac (non-inductive), 6A, 125V ac, 3A, 250V ac, 2A, 250V ac, 5A, 125V ac, Series 66 with suffixes, Series 65 with suffixes.
- 8A, 125V ac, 4A, 250V ac, 1A, 250V dc, Series P28 with Suffixes A to F or L to T, 900.
- 8A, 125V ac; 4A, 250V ac; 1/4 hp, 125-250V ac (Code 48) - RA---, RB---, RC---may have additional suffixes.
- 8A, 125V ac, 4A, 250V ac, 1/3 hp, 125-250V ac, NPA330, NPA331, NPA335, NPB330, NPB331, NPB335.
- 8A, 125V ac, 5A, 250V ac (or less to customer specification), S60A, S65A, S66A, S68A, S60B, S65B, S66B, S68B.
- 8A, 125V ac, 5A, 250V ac, 1/3 hp, 125-250V ac, TILA80 to TILA85, TILA8A to TILA8F, TILA8L, TILA8M, TILA8Q to TILA8T, TILB80 to TILB85, TILB8A to TILB8F, TILC80 to TILC85, TILC8A to TILC8F, TILC8L, TILC8M, TILC8Q to TILC8T, LTILA80 to 85, LTILB80 to 85, LTILC80 to 85, TIGM8T5.