

DIAL TORQUE WRENCHES - FT-LBS/MKG

Click to Zoom

- ▶ Accurate to $\pm 4\%$ of torque reading in both directions at 20% to 100% of full scale.
- ▶ Available in all steel or aluminum torque transfer components.
- ▶ High alloy torsion drive design — accuracy not effected by hand position.
- ▶ Dual scale (English/Metric) with clockwise and counterclockwise operation — fewer wrenches needed to complete job.
- ▶ Memory needles are standard on all wrenches except electric light models.
- ▶ Easy-to-read, high contrast scale.
- ▶ Laser marked serial number for traceability.
- ▶ N.I.S.T. (National Institute of Standards and Technology) traceable CW certification supplied with each wrench.
- ▶ J6133F and J6141F include one removable extension handle for easy force application.
- ▶ J6149F includes five removable extensions (requires two operators) and electric LED and buzzer.



J6113F



J6121F



J6133F



J6149F

Product #	Drive Size (in)	Torque Range (ft-lbs)	Torque Range (metric)	Increments (ft-lbs)	Overall Length (in)	Weight (lbs)
J6113F	3/8	10-50	1.4-7 mkg	1	10-1/4	2.20
J6121F	1/2	35-175	5-24 mkg	5	21-1/2	4.00
J6125F	1/2	50-250	7-35 mkg	5	21-1/2	3.80
J6134F	3/4	70-350	-	10	27-7/8	7.10
J6133F	3/4	120-600	16-80 mkg	10	46-1/2	9.90
J6141F	1	200-1000	28-140 mkg	20	74-1/4	27.00
J6149F	1	400-2000	56-280 mkg	40	110-3/4	48.00