
Features

- Wall-mounted group lock box with side-slider panel.
- Suitable for equipment with multiple lockout points.
- Heavy-duty steel construction.
- Clear polycarbonate viewing window.
- 12 internal key hangers for organised storage.
- Secure access only after removal of all applied locks.
- Pre-drilled for easy installation (hardware included).

RS PRO Wall Mount Group Lockout Box - Side Slider Yellow

RS Stock No.: 0802235



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- ***Designed for Multi-Point Group Lockout*** *- Ideal for teams performing lockout procedures on equipment with multiple isolation points, ensuring secure key control during maintenance.*
- ***Centralized Wall-Mounted Solution*** *- Designed for wall installation, creating a fixed and easily accessible lockout control station within the facility.*
- ***Durable Steel Construction*** *- Manufactured from heavy-duty steel for strength and long-lasting industrial performance.*
- ***Clear Polycarbonate Viewing Window*** *- Transparent front window allows supervisors to visually verify that keys for each lockout point are securely enclosed.*
- ***12 Internal Key Hangers*** *- Equipped with 12 dedicated internal hooks for organised key management and easy identification.*
- ***Secure Side-Slider Access Panel*** *- Keys remain inaccessible until all applied padlocks are removed. The sliding panel mechanism allows controlled access once the lockout is complete.*
- ***Easy Installation*** *- Supplied with pre-drilled mounting holes and necessary hardware for convenient wall mounting.*
- ***High-Visibility Powder-Coated Finish*** *- Standard yellow powder-coated finish for enhanced visibility.*

General Specifications

Type	Group Lock Box
Material	Steel & polycarbonate window
Colour	Yellow
Package	LD + Carton Box

Mechanical Specifications

Dimensions	161mm x 362mm x 154mm
Height	161mm
Width	362mm
Depth	154mm
Weight	1.9 Kgs

Operation Environment Specifications

Withstand temperature	-30°C to 120°C

