



Radial insert ball bearings GE25-XL-KRR-B (Series GE..-KRR-B)

spherical outer ring, location by eccentric locking collar, R
seals on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (<http://www.ina.de/content.ina.de/en/mediathek/library/library.jsp>) or by telephone on +49 (91 32) 82 - 28 97.

d	25 mm
DSF	52 mm
B ₁	44,5 mm
B	34,9 mm
C	15 mm
C ₂	16,7 mm
C _a	4,1 mm
D ₁	42,5 mm
d ₁	33,8 mm
d ₃ max	37,5 mm
S	17,5 mm
W	3 mm
Cur	395 N Fatigue limit load, radial
m	0,25 kg Mass
Cr	14900 N Basic dynamic load rating, radial
Co _r	7800 N Basic static load rating, radial
f ₀	13,8 Calculation factor

