




Power Cord, C19 to C20, 2.0m
Part Number: AP9877



Output	
Maximum Total Current Draw per Phase	20A
Output Connections	(1) IEC 320 C19 
Input	
Input Connections	IEC-320 C20
Cord Length	1.98 meters
Number of Power Cords	1
Maximum Line Current per phase	20A
Maximum Input Current per phase	20A
Physical	
Net Weight	0.36 KG
Shipping Weight	0.46 KG

Shipping Height	305.00 mm
Shipping Width	102.00 mm
Shipping Depth	102.00 mm
Color	Black

Conformance

Standard Warranty	2 years repair or replace
-------------------	---------------------------

Sustainable Offer Status

RoHS	Compliant
PEP	Available in Documentation tab
EOLI	Available in Documentation tab

⌵
*