

FEATURES

- **Non-Releasable Design:** Ensures a secure hold that won't loosen over time
- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight
- **High Tensile Strength of 36 kg:** Provides robust support for heavy-duty applications
- **UL 94 V-2 Fire Behaviour:** Offers a level of flame retardancy for added safety
- **Wide Operating Temperature Range:** Functions effectively up to 85 °C
- **Complies with RoHS Standards:** Environmentally friendly and safe for use in various settings
- **4.8 mm Width:** Balances strength and flexibility for versatile use

RS PRO 300mm Nylon Cable Tie, Non-Releasable

RS Stock No: 656-055



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO cable ties are designed for secure and efficient bundling of cables and wires. Made from durable nylon, they offer a reliable solution for organising and managing cable installations. With a maximum bundle diameter of 83 mm, these ties are suitable for a wide range of applications.

General Specifications

Colour	Natural
Product Type	Cable Tie
Sub Type	Non-Releaseable
Tensile Strength	36 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	300 mm
Material	Nylon
Maximum Bundle Diameter	83 mm
Width	4.8 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---

