

## Ha-EIZ4 RJ45S-3.0M/KETH



Image is for illustration purposes only. Please refer to product description.

Part number	72 MD M4R M403 0K
Specification	Ha-EIZ4 RJ45S-3.0M/KETH
HARTING eCatalogue	<a href="https://harting.com/72MDM4RM4030K">https://harting.com/72MDM4RM4030K</a>

### Identification

Category	System cabling
Series	RJ45 Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	RJ45
Connector 2	M12 D-coding Male
Type of cable	Copper cable (round)

### Version

Cable length	3 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

### Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +80 °C

### Material properties

Material (cable)	PVC
------------------	-----



**Pushing Performance**  
Since 1945

## Material properties

Colour (cable)	Green
----------------	-------

## Specifications and approvals

Approvals	CE
PROFINET	Yes

## Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85444290
GTIN	5713140268234
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600