



CSB Twin Pack 190 x 24T/48T - 2pc

CIRCULAR SAW BLADES FOR HAND HELD CIRCULAR SAWS

- PTFE coating: Cuts cooler, non stick for quicker cuts. Protects against corrosion and accumulation of resin.
- Laser cut vibration slots: Low vibration and increased accuracy.
- High grade laser cut steel: Guaranteed accuracy.
- Premium cobalt infused tungsten carbide: Sharp and clean cuts.
- Thin Kerf: Cordless optimised, extra thin cutting width for maximum runtime
- All wood types: Soft/ hardwood, plywood, laminated chipboard, melamine, MDF
- **Standard blades without PTFE coating and vibration slots



All Wood Types	✓
Article Number	4932479574
Blade diameter (mm)	190
Bore size (mm)	30
Clean Cut	✓
Contents	1 x 190x30x24 tooth, fast cut wood blade (4932471300) + 1 x 190x30x48 tooth, clean cut wood blade (4932471380)
Cutting width (kerf) (mm)	1.6/2.1
Hook Angle	+15°/+10°
Materials suited for	Wood with nails & screws Green wood Wood Particleboard, Fibrecement board, Fibreglass