



**Part Number :** [1301060112](#)

**Product Description :** Super-Safeway Molded Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead 5 Sockets, NEMA 5-15 Plug, Overall Length 15.24m (50.0')

**Series Number :** 130106

**Status :** Active

**Product Category :** Lamps and Lights

**Engineering Number :** 323523



---

## Documents & Resources

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Lamps and Lights
Series	130106
Description	Super-Safeway Molded Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead 5 Sockets, NEMA 5-15 Plug, Overall Length 15.24m (50.0')
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Product Name	Super-Safeway
Type	String Lights
UPC	78678879893

### Electrical

Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

### Physical

Bulb Type	Incandescent
Cord Length - Primary	1.52m (5.0')
Cord Length - Secondary	1.52m (5.0')
Cord Type - Primary	12/3 SOOW
Depth	47.625mm (1.875")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	107.95mm (4.250")
Lamp Type	A21
Length	15.24m (50.0')
Material - Guard	N/A
Mounting Style	Stringer

Net Weight	6014.634/g
Outlet	None
Packaging Type	Carton
Socket Construction	Rubber Molded

---

This document was generated on Sep 24, 2025