

Product data sheet

179 N-7/220

EAN-No. 4000896220267



220-pieces · 7 Drawers total



Application:

Efficient, mobile organisation of tools

- Tool trolley
- 5 flat and 2 high drawers

Work areas

- Much larger storage and work areas in plastic (179N) or stainless steel (179NX)
- Fully sealed work surface protects inside of trolley from leaking liquids
- Interfaces integrated in the work area for accessories such as laptop holders and top modules

Body / Pull-handle

- Extremely robust design thanks to dual-wall structure
- Complete welded construction of the entire body for tough daily workshop use
- Optimised, yielding edge protection on all four corners with real impact protection thanks to internal damping concept
- Ergonomically optimised pull handle for better manoeuvrability

Locking concept

- Ergonomically arranged side lock position for better operability protects keys and lock against damage
- Highly secure closing system with central locking technology for optimum protection of your property
- 2-stage locking
 - Central locking, lockable with cylinder lock and 2 folding keys
 - Mutual drawer locking for minimum tilting risk

Drawer concept

- Self-closing and reciprocal locking of the drawers prevents unwanted opening
- 100% sliding-out with ball-bearing telescopic slides
- Drawer design for optimum use of the interior
- Drawer fronts for optimised handling
- Dirt-resistant drawer coating for easy cleaning

High performance chassis

- Large wheels with high loading capacity, precision ball bearing and dual rounded rim in the pivot bearing, easy manoeuvrability, even with high dynamic load
- 2 swivel castors with dual brake:
 - Braked castors prevent rolling away
 - Braked swivel bearings prevent the swivel castors from turning, e.g. on inclined surfaces
- Protective ring prevents dirt and threads from getting in
- Elastic castors enable smooth movement

Assistant 179N-6 – 9:

EAN-No. 4000896**220267**

- Solvent-resistant plastic work surface
- Metal handle, powder coated in black

Assistent[®] **179NX-6 – 8:**

- Stainless steel work surface
- Extra protection through high-quality plastic end caps
- Brushed stainless steel handle
- Total loading capacity (dynamic): 540 kg
- Loading capacity (static): 1000 kg
- Loading capacity of high drawer: 25 kg
- Colour: HAZET blue
- Tool trolley Made in Germany
- Dimensions: 785 mm x 518 mm x 1020 mm
- Net weight: 87.2 kg
- Drawers, flat: 5× 81 x 522 x 398 mm
- Drawers, high: 2× 166 x 522 x 398 mm
- (Drawer) size for plastic drawer insert: 3/3+
- Worktop: Plastic, resistant to solvent, with integrated storage wells
- Number of fixed castors: 2 (Ø 125 mm)
- Number of swivel castors: 2 (Ø 125 mm)
- Number of tools: 220

[illegible]

Product data sheet

179 N-7/220

EAN-No. 4000896220267



600N • •
6 • 7 • 8 • 9 • 10 • 11 • 12 •
13 • 14 • 15 • 16 • 17 • 18 •
19 • 21 • 22 • 24

630 • •
6 x 7 • 8 x 9 • 10 x 11 •
12 x 13 • 14 x 15 • 16 x 17 •
18 x 19 • 21 x 22



163-141/31N

• • •

802 • •
1.6 x 10 • 2 x 12 • 0.6 x 3.5 •
0.8 x 4 • 1 x 5.5 • 1.2 x 6.5 •
1.2 x 8

802-PH • •
PH1 • PH2 • PH3



811T • •
T10 • T15 • T20 • T25 •
T27 • T30 • T6 • T7 • T8 • T9



811K • •
1 x 5.5



811KPH • •
PH2



2105LG/9H •



163-143/18N •

612N • •
10 x 11

730
730-3 • 730-6

746-1

748B
748B-3 • 748B-4 • 748B-5 •
748B-6 • 748B-8



811F • •
6 • 7

824 • •
0.5 x 23



1952-40

2140-40



2152N/3



2154N-5



4968-2



2128N-1



2240N/36
 • • • • • • •

2204N • • • •
3 • 4 • 5 • 6

2208N • • • •
0.6 x 4.5 • 0.8 x 5.5 • 1 x 6

2215N • • • •
PH1 • PH2 • PH3

2216N • • • •
PZ1 • PZ2 • PZ3

2223N • • • •
T10 • T15 • T20 • T25 •
T27 • T30 • T40

2223N • • • •
T20H • T30H



2239N-6 • • •