


# 3-Channel Yellow Jacket® Cable Protector for 2.125" Lines - YJ3-225-Y/B

## Product Images



## Short Description

- Protects cables and hoses up to 2.125" outside dia.
- The "Original" cable protector
- Dog bone connectors to extend to any desired length
- Thick lid and base allow for high volume of traffic
- Hinged lid for easy cable placement
- Modular interlocking design
- Ideal for use in industrial, commercial, and public applications
- Personalize cable protectors with your logo or colors. [Request a quote now.](#)

## Description

---

YELLOW JACKET® 3-CHANNEL CABLE PROTECTOR with hinged lid provides a safe crossing in high volume traffic areas while protecting valuable electrical cables and hose lines from damage. Modular interlocking design is ideal for use in industrial, commercial, and public applications.

Personalize cable protectors with your logo or colors. [Request a quote now.](#)

## Specifications

---

Model No	YJ3-225-Y/B
UPC	812958008973
Brand	Checkers Safety™
Color	Yellow Lid / Black Base
Quantity Included	1
Load Capacity Per Axle	28420 lbs
Length (Inches)	36
Width (Inches)	18.5
Height (Inches)	2.875
Max Cable Outside Diameter (Inches)	2.125
Number of Channels	3-Channels
Connector Type	Dog Bone Connector
Channel Width	2.125

## Prop 65

---

**⚠️WARNING:** This product can expose you to chemicals including Carbon Black, Titanium Dioxide, Formaldehyde, and Benzyl Butyl Phthalate, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).