

FEATURES

- Excellent resistance
- Greater load carrying capacity
- Self-locking
- Easy to install
- Roller ball design which is self-locking and fast

RS PRO Steel Stainless Steel Roller Ball Cable Tie, 360mm x 12mm

RS Stock No.:123-5029



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO stainless steel cable ties are an ideal alternative where Nylon 66 cable ties are not suitable such as harsh environments or places where there is heat. These cable ties have a roller ball design which is self-locking and fast and easy to install. Roller ball ties have a locking ball bearing which grips the tie strap and locks the tie as it is tensioned.

General Specifications

Type	Roller Ball
Colour	Steel
Material	Stainless Steel
Application	General Strapping application
Resistant To	Corrosion, radiation and abrasion, uv light
UV Resistant	Yes
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	300°C
Fire Behaviour	Halogen Free

Mechanical Specifications

Length	360mm
Width	12mm
Tensile Strength	114kg
Maximum Bundle Strength	100mm

Approvals

Standards Met	UL-94V-2
----------------------	----------

