



tesa® 4324

Product Information



Flexible finely crêped paper masking tape

Product Description

tesa® 4324 is a finely crêped and wet resistant paper masking tape with a good flexibility and a high tensile strength.

Sustainable Aspects



For more information: <https://www.tesa.com/product-sustainability>

Product Features

tesa® 4324 is a highly crêped and wet resistant paper masking tape with a good flexibility and a high tensile strength.

Application Fields

tesa® 4324 is suitable for masking during paint spraying with oven drying (up to 80 °C).

Further applications are e.g.:

- bandoliering of yarn beams
- splicing of photo papers and veneers
- coil bandages

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|-----------------------|--|--------|
| • Backing material | slightly-creped paper | • Bio-based content of liner by weight (acc. EN 16785) | 48 % |
| • Type of adhesive | natural rubber | • Total thickness | 280 µm |

Properties/Performance Values

- | | | | |
|-----------------------|---------|-----------------------------------|-----------|
| • Elongation at break | 17 % | • Hand tearability | very good |
| • Tensile strength | 46 N/cm | • Temperature resistance (60 min) | 80 °C |
| • Easy to remove | yes | | |

Adhesion to Values

- | | |
|---------|--------|
| • steel | 4 N/cm |
|---------|--------|

For latest information on this product please visit <http://l.tesa.com/?ip=04324>



tesa[®] 4324

Product Information

Additional Information

The flexibility and the soft adhesive allow good adhesion to rough surfaces or complicated shapes and contours.

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?ip=04324>