

PREVOST FILTRATION - SINGLE UNITS

Lubricator



Part number	Female thread	Flow rate at 6.00 bar (l/min) ($\Delta P = 0.30$ bar)	Temperature min/max (°C)	Max. operating pressure (bar)	Net weight (Kg)
ATU L100	G1/8	600.00	5.00 / 50.00	10.00	0,323
ATU L101	G1/4	950.00	5.00 / 50.00	10.00	0,323
ATU L102	G3/8	2400.00	5.00 / 50.00	10.00	0,876
ATU L103	G1/2	4000.00	5.00 / 50.00	10.00	0,876

