

Eaton 248338

Catalog Number: 248338

Eaton Distribution parts. Control switchp13 S, 1 N/C, 16A, 230 V, 20kA

General specifications



Product Name

Eaton Distribution parts

Catalog Number

248338

EAN

4015082483388

Product Length/Depth

80 mm

Product Height

75 mm

Product Width

17.5 mm

Product Weight

0.085 kg

Compliances

RoHS conform



Powering Business Worldwide

Product specifications

Rated operational voltage (Ue) - max

240 V

Voltage rating - min

0 V

Width in number of modular spacings

1

Number of poles

Four-pole

Color calotte

Other

Switch type

Control switch

Rated short-time withstand current (Icw)

10 kA

Lamp socket

Other

Built-in depth

80 mm

Amperage rating

20 A

Voltage type

AC

Lamp type

Other

Degree of protection

IP40

Lamp power

0 W

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

1

Number of contacts (normally open contacts)

3

Inscription

Resources

Declarations of conformity

[DA-DC-03_Z-S_SC_SB](#)

[DA-DC-03_Z-S](#)

Drawings

[eaton-wiring-diagram-zx-ss.jpg](#)

[eaton-dimensions-mas-z-s.jpg](#)

[eaton-mcb-dimensions-122x115.eps](#)

[122I160](#)

Other

Rated operational current for specified heat dissipation (In)

20 A

Rated Switching Capacity

0.02 kA



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia