

Features

- IEC-584-3
- Fast response, welded exposed junction
- Bare tails termination

RS PRO PTFE insulated Twin Twisted IEC Exposed Junction Thermocouple with Bare Tails - Type K

RS Stock No.: 0652748



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Fast response welded exposed junction available with bare tails. Ideal for test & development applications.

General Specifications

Thermocouple Type	Type K
Temperature Measurement Range	-75°C to +260°C
Construction	Terminated with bare wire
Measuring Junction	Exposed
Standards Met	IEC
Application	Fast response, welded exposed junction

Mechanical Specifications

Termination	Bare wire
Length	0.3m (0.98ft)
Cable Insulation	1/0.2mm PTFE insulated Twin Twisted

Approvals

Declarations	RoHS
--------------	------

Similar Products

Colour Code	Type	Style	Cable Size	Length	Termination	RS Stock#
IEC	J	PTFE	1/0.2mm	1m (3.3ft)	Bare Tails	2713132
IEC	J	PTFE	1/0.2mm	2m (6.56ft)	Bare Tails	2713133
IEC	J	PTFE	1/0.2mm	3m (9.84ft)	Bare Tails	2713134
IEC	J	PTFE	1/0.2mm	5m (16.4 ft)	Bare Tails	2713135
IEC	J	PTFE	1/0.2mm	10m (32.8ft)	Bare Tails	2713136
IEC	K	PTFE	1/0.2mm	0.3m (0.98ft)	Bare Tails	0652748
IEC	K	PTFE	1/0.2mm	1m (3.3ft)	Bare Tails	2713137
IEC	K	PTFE	1/0.2mm	2m (6.56ft)	Bare Tails	2713138
IEC	K	PTFE	1/0.2mm	3m (9.84ft)	Bare Tails	2713139
IEC	K	PTFE	1/0.2mm	5m (16.4 ft)	Bare Tails	2713140
IEC	K	PTFE	1/0.2mm	10m (32.8ft)	Bare Tails	2713141
IEC	T	PTFE	1/0.2mm	0.3m (0.98ft)	Bare Tails	0652749
IEC	T	PTFE	1/0.2mm	1m (3.3ft)	Bare Tails	2713142
IEC	T	PTFE	1/0.2mm	2m (6.56ft)	Bare Tails	2713143
IEC	T	PTFE	1/0.2mm	3m (9.84ft)	Bare Tails	2713144
IEC	T	PTFE	1/0.2mm	5m (16.4 ft)	Bare Tails	2713145
IEC	T	PTFE	1/0.2mm	10m (32.8ft)	Bare Tails	2713146