Cutting-off wheel

A 960 TZ *SPECIAL*



Properties

Bonding agent	Synthetic resin, fibre-reinforced
Type of grain	Aluminium oxide
Bond	■■■■■■
Aggression	■■■■■■□
Service life	■■■■■■

Materials

Stainless steel	●
Steel	●

Product benefit

Free of iron, sulphur and chlorine - Short cutting times and long service life - Low thermal load - Low burr formation - Optimized bonding for considerably longer service life - For diverse applications - 25 pieces delivered in the Kronenflex® box for long lasting high performance and moisture protection

Applications

- Plant engineering
- Apparatus and container manufacturing
- Metal construction
- Locksmith's shop
- Stainless steel processing industry
- Railing construction

Diameter x Width x Bore in mm	Form	Vmax m/s	Max. RPM	Packing unit/pcs.	Cat. number
115 x 1 x 22,23	▬	80 m/s	13300 rpm	25	322180
125 x 1 x 22,23	▬	80 m/s	12250 rpm	25	322181

Klingspor Schleifsysteme GmbH und Co. KG
Hüttenstraße 36 - 35708 Haiger - Germany
Fon + 49 (0) 2773 922-0 Fax + 49 (0) 2773 922-186
sales@klingspor.de - www.klingspor.de