



TECHNICAL CHARACTERISTICS

MATERIAL  
 CONTACT MATERIAL: COPPER ALLOY  
 CONTACT TYPE: STAMPED  
 CONTACT PLATING: TIN  
 QUALITY CLASS: 25 MATING CYCLES  
 PITCH: FOR 4.20MM

ENVIRONMENTAL  
 OPERATING TEMPERATURE: -40 UP TO 105°C  
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL  
 CURRENT RATING: 6 TO 9A  
 WORKING VOLTAGE: 600V AC  
 INSULATOR RESISTANCE: >1000 MOHM  
 DIELECTRIC WITHSTANDING VOLTAGE: 1500V AC/MN  
 CONTACT RESISTANCE: 10 MOHM MAX

WIRE DIMENSION  
 64910913722 AWG 18-24

PACKAGING  
 REEL OF 200 PCS

DIMENSION

ORDER CODE	AWG	A	B	C	D
64910913722	18-24	3.60	4.50	1.90	2.30

RoHS Compliant			
G			
F			
E			
D			
C			
B	13-FEB-14	CORRECTIONS	QL
A	09-MAR-11	CREATION	GG
REV	DATE	FILE	BY

PROJECTION:
APPROVAL: RJ

GENERAL TOLERANCE
.X = +/- 0.2
.XX = +/- 0.15
UNIT: MM
SCALE:
SHEET: 1/2
DRAW: MIKE

DESCRIPTION: 4.2MM MALE CRIMP TERMINAL 18-24 AWG	SIZE
WERI PART NO: 649 109 137 22	<b>A4</b>