



tesa® 4414

Product Information



Strong PE Surface Protection Tape

Product Description

tesa® 4414 consists of a UV stabilized PE backing and a high tack, removable acrylic adhesive. The blue translucent color provides a good contrast to surfaces and eases tape detection.

The excellent continuous outdoor stability for up to 6 months allows clean removal in a wide range of protection applications whenever strong resistance against mechanical damage is required. Therefore it is especially suited for surface protection jobs in transportation sectors such as railway, marine, special vehicles during assembly, storage and transportation.

Product Features

- Excellent visibility due to blue translucent color
- The high tack adhesive provides good quick stick to a wide range of surfaces
- Residue free removable up to 6 months even after continuous outdoor use
- Strong PE backing for good resistance against mechanical damage
- Easy to apply due to low backing elongation when unwind
- Temperature resistance up to 70°C / 1h

Application Fields

- For temporary masking and protection of coated surfaces such as aluminium, metal, glass and other substrates during assembly, storage and transportation whenever residue free removability is required.
- The temperature resistance makes it also suitable for overmask applications during spray painting with subsequent oven drying up to 70°C. Paint overspray adheres well to the polyethylene backing.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|---------------------|-------------------|--------|
| • Backing | PE film | • Total thickness | 150 µm |
| • Type of adhesive | water-based acrylic | | |

Properties/Performance Values

- | | | | |
|-----------------------|---------|--------------------|------|
| • Elongation at break | 400 % | • Hand tearability | good |
| • Tensile strength | 23 N/cm | | |

Adhesion to Values

- | | |
|---------|----------|
| • Steel | 2.2 N/cm |
|---------|----------|

For latest information on this product please visit <http://l.tesa.com/?ip=04414>



tesa[®] 4414

Product Information

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=04414>