

FEATURES

- Un-Coated
- 316 / 316 L grade
- Self Locking
- Rust Free
- Low Insertion force

RS PRO cable tie

RS Stock No.: 743-6399



Product Description

Roller Ball Cable Tie

SS440XHD

ved Products bring to you professional product categories. Our product range eers and provides a comparable quality out paying a premium price.

Stainless Steel Cable Ties



Applications:

- Installation of Cables and Pipes in Extreme conditions and Hazardous area.
- Petrochemical, food processing industries, power stations, mining, shipbuilding, offshore and other aggressive environments.

General Specifications

Mechanical Specifications:

опанова оргонованова	
Width [mm]	12.0
Thickness [mm]	0.32
Length/s [mm]	440
Loop Tensile Strength	2002 N
Operating Temperature [max]	300° C
Operating Temperature [min]	-40 °C
UV Resistant	Yes
Un-Coated	Yes

Electrical Specifications

Protection Category	

Classification

Stainless Steel Cable Ties



eCI@ss (Version)	
UNSPSC(Version)	

Approvals

Declarations	MFR Declaration of Conformity		
Hazardous Area Certification	ATEX / IECEx		
Standards Met	UL 62275 ; IEC 62275		

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
XXX-XXXX	RS PRO				
XXX-XXXX	RS PRO				

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories