

415CO-A
Twist drills with cylindrical shanks, short series, HSS-CO 5%, entirely ground, small tang (ø 13 mm)
DIN 338

 R ≤ 1200 N/mm²
 HV ~ 800÷860

	art.	L1 mm	L mm	ø mm
004150364	415CO-A 14,00	108	160	14,00
004150366	415CO-A 15,00	114	169	15,00
004150368	415CO-A 16,00	120	178	16,00
004150370	415CO-A 17,00	125	184	17,00
004150372	415CO-A 18,00	130	191	18,00
004150374	415CO-A 19,00	135	198	19,00
004150376	415CO-A 20,00	140	205	20,00

