

## Cam rollers



Dimensions			Basic load ratings		Fatigue load limit	Maximum radial loads		Limiting speed	Mass	Designation
D	d	B	dynamic C	static C <sub>0</sub>	P <sub>u</sub>	dynamic F <sub>r</sub>	static F <sub>0r</sub>			
mm			kN		kN	kN		r/min	kg	-
72	30	23,8	27	17	0,71	17,3	24,5	5000	0,48	305806 C-2Z

