



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-293774-1
NECTOR M PIN HSG PANEL MOUNT
7P CODE A

Customers Also Bought



TE Part #2826923001
44A0111-18-95



TE Part #CQ81973001
100G1131-1.00-0/5/9-0



TE Part #BTH1-21-10-1-ZN-SB
BTH1-21-10-1-ZN-SB



TE Part #2318136-6
TWO-PIECE POKE-IN, 8MM HEADER,
6 POS




TE Part #2318136-6
TWO-PIECE POKE-IN, 8MM HEADER,
6 POS



TE Part #1892787-9
Assy Vert MINIPAK HDL Rcpt 20s



TE Part #BTH3-21-10-1-ZN-SB
BTH3-21-10-1-ZN-SB



TE Part #102920-2
MOD IV RECP LP



TE Part #CAT-D38999-DTS19T
Straight Plug: D38999, 25-37 Insert,
Electroless Nickel Plating



TE Part #2213585-2
NECTOR M 3PSN PUSH DE-LATCH
TOOL

Documents

Product Drawings

NECTOR M PIN HSG PANEL MOUNT 7P CODE A

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_293774-1_A_c-293774-1-a.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_293774-1_A_c-293774-1-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_293774-1_A_c-293774-1-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English