



Product data sheet

Power tools for trade & industry

Mitre Saw

PRO GCM 340-305 D



The heavy-duty, high-performance miter saw with long-lasting accuracy

The most important data

Saw blade diameter	305 mm
Mitre setting	52 ° L / 60 ° R
Bevel setting	47 ° L / 47 ° R

Part Number 0 601 B60 070

Technical data

Technical data

Cutting capacity, 0°	105 x 340 mm
Cutting capacity, 45° mitre	105 x 245 mm
Cutting capacity, 45° bevel	340 mm
Mitre setting	52 ° L / 60 ° R
Bevel setting	47 ° L / 47 ° R
Tool dimensions (width x length x height)	617 x 885 x 709 mm
No-load speed	4,050 rpm
Saw blade diameter	305 mm
Saw blade bore diameter	30 mm
Weight	21.4 kg
Rated input power	1,800 W
Voltage	220 – 240 V
Packaging dimensions (width x length x height)	520 x 950 x 550 mm

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Long-term accuracy thanks to integrated LED light system with reliable cutting-line indication. Easy workpiece control for different material sizes due to detachable workpiece support and long extensions. Effortless cutting – even for large pieces of wood – thanks to strong cutting capacity driven by powerful motor



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

