

## **RS Pro Datasheet – Fiche Technique – Datenblatt**

RS Pro: 144-8606




VALUE Mini DisplayPort Cable, Mini DP-HDTV, M/M, black, 2.0 m

VALUE Mini DisplayPort Câble, Mini DP - HDTV, M/M, noir, 2.0 m

VALUE Mini DisplayPort Kabel, Mini DP-HDTV, ST/ST, schwarz, 2.0 m

| FILE AMEND NOTE  | DATE        | REV. |
|------------------|-------------|------|
| ORIGINAL EDITION | May 18 2017 | B/0  |



PRINTING: DisplayPort E324703 AWM STYLE 20276 80 30V VW-1

## NOTE:

### 1.Electrical properties:

- 1.ALL COMPONENTS ARE RoHS COMPLIANT.
- 2.100% OPEN AND SHORT TEST.
- 3.CONDUCTOR RESISTANCE:3 OHMS
- 4.INSULATION RESISTANCE:10 MEGOHMS.
- 5.HI-POT:DC200V/0.01S
- 6.PC TEST 4K\*2K 30Hz PASS 1080P PASS

### 2. ROHS 2.0 and REACH

## MODEL LIST

| Model      | Length | DSP        |
|------------|--------|------------|
| 11.99.5790 | 1000mm | 4K*2K 30HZ |
| 11.99.5791 | 2000mm | 4K*2K 30HZ |
| 11.99.5792 | 3000mm | 4K*2K 30HZ |
| 11.99.5793 | 4500mm | 4K*2K 30HZ |

## MATERIAL LIST

| No. | PART NAME  | DESCRIPTION                                                                | QTY |
|-----|------------|----------------------------------------------------------------------------|-----|
| ⑤   | CABLE      | [(32AWG*1P)+D+AM]*5PCS+32AWGX4C+AM+ALMG+PVC<br>OD: 5.0±0.1mm, COLOR: BLACK | L   |
| ④   | OUTER MOLD | BLACK PVC                                                                  | 1   |
| ③   | OUTER MOLD | BLACK ABS                                                                  | 1   |
| ②   | CONNECTOR  | HDMI Male, Nickel plated                                                   | 1   |
| ①   | CONNECTOR  | MINI DISPLAYPORT 20P Male, Nickel plated                                   | 1   |
| No. | PART NAME  | DESCRIPTION                                                                | QTY |

| DRAW No.   | NAME       | VALUE     | Mini DP Cable, Mini DP-HDTV, M/M, black |
|------------|------------|-----------|-----------------------------------------|
| CUSTOMER   | MAPE       | TOLERANCE | X. ±1.00<br>X.X ±0.50                   |
| MODEL No.  | 11.99.579X | SCALE     | MM                                      |
| APPROVE BY | CHECK BY   | DRAW BY   | PAGE 1/1                                |