

Roof fan, Extract: W: 292 mm, H: 292 mm, RAL 7035, IP54, Airflow: 550 m3/h, Ue AC: 115 V



| Model                                    |                  |
|------------------------------------------|------------------|
| product brand name                       | SIVACON          |
| product designation                      | Roof fans        |
| type of ventilation                      | ventilation      |
| fan design withdrawable fan              | No               |
| design of the product EMC version        | No               |
| General technical data                   |                  |
| A-rated sound power level maximum        | 55 dB            |
| consumed active power rated value        | 64 W             |
| cutout width                             | 292 mm           |
| cutout height                            | 292 mm           |
| operating period                         | 40 000 h         |
| rotor speed at 50 Hz rated value         | 0.58 1/min       |
| rotor speed at 60 Hz rated value         | 0.7 1/min        |
| type of voltage of the operating voltage | AC               |
| consumed current maximum                 | 0.35 A           |
| operating voltage                        |                  |
| • at AC at 50 Hz rated value maximum     | 115 V            |
| • at AC at 60 Hz rated value maximum     | 115 V            |
| Protection class                         |                  |
| protection class IP                      | IP54             |
| Appearance                               |                  |
| color                                    | light grey       |
| Product details                          |                  |
| product component fan                    | Yes              |
| Number                                   |                  |
| number of ventilators                    | 1                |
| Mechanical Design                        |                  |
| height                                   | 361 mm           |
| width                                    | 361 mm           |
| depth                                    | 211 mm           |
| installation location                    | roof             |
| fastening method                         | snap-on mounting |
| fastening method                         |                  |
| • 19-inch installation                   | No               |
| • wall mounting                          | No               |
| net weight                               | 4.4 kg           |
| material                                 | plastic          |
| ambient temperature during operation     |                  |
| • minimum                                | -10 °C           |

• maximum

55 °C

## Approvals Certificates

General Product Approval

other

Environment



[Confirmation](#)

[Environmental Con-  
firmations](#)

## Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6411-5VL60>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6411-5VL60>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MR6411-5VL60](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6411-5VL60)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

