

Panel Antenna 2,4 GHz, 16 dBi

Product ID: 700-889-ANT05

Edition 1 (10.07.2024)



Cable outlet on the rear.

Fastened using enclosed metal bracket for pipe mounting.

For indoor and outdoor installation.

Technical Data:

Frequency range	2,4 – 2,5 GHz
Gain	16 dBi
Impedance	50 Ohm
Polarization	horizontal + vertical
Connection	N-Type (f)
Size (L x W x H)	280 x 210 x 90 mm
Weight	350 g
Protection class	IP 67

Subject to technical changes.