



PINOUT:

| PAIR | P1 | COLOR | P2 |
|------|-------|-------|-------|
| 1 | 2 | WHITE | 2 |
| | 3 | GREEN | 3 |
| | 1 | RED | 1 |
| | 5 | BLACK | 4 |
| | SHELL | DR+BR | SHELL |

| PRODUCT NO. | LENGTH(xx) |
|-------------|--------------|
| USB2HABM3LA | 915+20/-0mm |
| USB2HABM6LA | 1830+25/-0mm |

- SPEC:
- CABLE: UL 2725 28AWG*1P+28AWG*2C+ADB(BRAID:MAGNESIUM)
JACKET BLACK IN COLOR OD:3.8MM
 - P1 CONNECTOR: MINI USB "B" TYPE 5PIN MALE SHELL NICKEL PLATED
 - P2 CONNECTOR:USB "A" TYPE 4PIN MALE SHELL NICKEL PLATED
 - MOLDING PE TRANSPARENT
 - MOLDING PVC BLACK IN COLOR

THIRD ANGLE PROJECTION

StarTech.com

| GENERAL NOTES | |
|-------------------------------------|---|
| DIMENSIONS ARE IN MM - DO NOT SCALE | |
| PRODUCT ID | USB2HABMxxLA |
| DESCRIPTION | Mini USB Cable - A to Left Angle Mini B |
| DO NOT SCALE | SHEET: 1 OF: 1 |
| UPLOAD DATE: 11/11/2020 | |