

Datasheet

**RS Pro Galvanised Steel Adjustable Height Mount 200mm
Rubber 33mm 4000kg
RS Stock No: 442-640**



Product Details

RS Pro galvanised steel adjustable height mount is designed to have a stabilizing and damping effect on installations of engineering machinery, scales and unsteady equipment. The design of the disc machine mount consists of a pressure plate made of galvanised sheet steel, which rests on a anti-vibration base element of impervious rubber. This simple yet functional design gives the mounts a very low installation height and a long service life.

Features and Benefits

- Damping machine mount for machines with built in levelling screws
- Low installation height
- 4000 kg static load capacity
- Rubber foot



ENGLISH

Specifications:

Base Material	Galvanised Steel
Diameter	200 mm
Foot Material	Rubber
Overall Height	33 mm
Static Load Capacity	4000 kg