

BLAZE -Specialities Spirapoints
Spirapoints BLAZE-9.525x38.1#120

Artical Number: 66261194491

EAN: 3157629493403

Description

The BEST choice for hard-to-grind materials, stainless steel, cobalt, inconel and titanium. Used on inside surfaces and corners where other abrasive shapes cannot reach and dressing fillet weld seams on metal structures. Typically these are used on high-speed air grinders and are always mounted on a mandrel. Ideal for flash removal, polishing, or removing machine tool marks, and edge breaking. A compact, lightweight, handheld tool for mandrel-mounted abrasive products that allows for better control than larger die grinders and is a must for any detail work on small parts. Cartridge and Spiral rolls are strips of abrasive cloth rolled and glued to form a solid shape that is designed to break down during use and reveal the next layer of abrasive. Easy to control and to replace due to special mandrel.

Features

Next-generation Ceramic Alumina abrasive grain
Advanced gridding aid
Improved resin bond system
Strong X-weight cotton backing

Benefits

Provides greatest productivity with significantly faster cut rates and longer life
For cooler cut and reduces loading and glazing
For exceptional grain retention and longer life
For durability and even wear

Application Data

Material Application: STEEL
Machine: Die Grinder
Process: Sanding
Equipments:

Technical Data

MarketingCAP:	R920	Diameter:	9.525 mm
BackingMaterial:	Heavy Cotton X	Length:	38.1 mm
Grit:	120		
Color:	Orange		
CoatedShape:	Coated Specialities		
CoatedSubShape:	Spiral rolls		
		Shape	

Logistic Data

Naked Product Weight	0.020 kg	Packed Product Dimension	230.000 mmx280.000 mmx1.000 mm
Naked Product Dimension	9.525x38.1	pack Qty (parts per pack)	100 pc
Units per part	1 pc	Packed Product Weight	0.025 kg