

## SB 183 7 TC S-001

### Pliers wrench set

incl. protective jaws

Code  
3112438

ETIM  
EC011919

EAN  
4010886956199

UNSPSC  
27-11-17-14

Country of origin  
Austria

eCl@ss  
21-04-01-90

Customs tariff number  
82032000



### Article description

- One tool that works like a spanner and pliers
- DIN ISO 5743
- Can replace two complete open-ended spanner sets, metric and inch (0-42mm/0-1.5/8")
- Careful assembly of bolt connections with delicate surfaces (e.g. chrome-plated fittings)
- Adjustable, universal tool for bolting
- Perfect for bending, holding, pressing and gripping a wide range of applications
- Play-free positioning with no risk of damaging the edges
- Sliding mechanism and paralleled jaws for quick and easy adjustment, practically stepless
- Secure locking of the setting when the size of the opening is selected
- Sliding mechanism may be activated from almost any setting
- May be used as a "ratchet spanner" – quick and easy tightening and loosening of hexagonal screws and nuts
- High ratio (> 1:10) for high pressing and clamping force against the jaws
- Made of GEDORE special hardened and tempered steel for the highest loads
- Can be used as a powerful vice when on the move
- Optimum ergonomic adjustment of the hand position to the size of the jaw or spanner opening
- Protection jaws available as an option • TL = steel-grey, with blue dipped non-slip handles
- TC = chrome-plated, with blue dipped handles

### Article information

|                          |                    |                             |                    |
|--------------------------|--------------------|-----------------------------|--------------------|
| Contents (Qty of pieces) | 1                  | Size [Inch]                 | 7                  |
| Net weight [kg]          | 0,265 kg           | Handle design               | dip-insulated      |
| Total length [mm]        | 190 mm             | Clamping width [mm]         | 42 mm              |
| Total width [mm]         | 49 mm              | Clamping width [inch]       | 1.5/8 "            |
| Total height [mm]        | 17 mm              | Baking mold                 | flat jaws          |
| Surface                  | chrome-plated      | Joint types                 | push-through joint |
| Material                 | Heat-treated steel | Jaw length L3 [mm]          | 25 mm              |
| Standard                 | DIN ISO 5743       | Head thickness [mm] T1      | 7,0 mm             |
| Head height l [mm]       | 25 mm              | Handle colour               | blue               |
| Width of head l [mm]     | 40,0 mm            | Thickness of point          | 3,0 mm             |
| Design non-sparking      | No                 | Number of setting positions | 18                 |
| Total length [inch]      | 7                  |                             |                    |