

MACCROSSROAD 3.0 S3 HIGH / 67313 / EN 20345:2011 S3 CI HI HRO SRC //

**100%
metal
free**

High safety shoe

- multipurpose
- slip resistance
- cushioning
- HRO
- comfort
- flexibility
- durability
- antistatic
- 100% metal free
- sizes: 36 - 48



APPLICATIONS //

energy | environment | services | construction | industry | heavy industry | agriculture & green spaces

TECHNICAL SPECIFICATIONS //

- **sole:** MACSOLE® ADVENTURE 3.0 rubber with MACABSORB EVA insert in forefoot and heel for greater flexibility and better cushioning | excellent levels of grip (SRC) | oil, hydrocarbon and chemical-resistant | antistatic | resistance to contact heat up to 300°C (HRO) | sole profile with ergonomic shapes to better follow freedom of movement | all-terrain profile with deep treads for better grip | rubber scuff cap
- **upper:** water-resistant full-grain leather | reinforced heel and sides Agile Ankle Guard for better stability and protection of malleolus while keeping high freedom of movement
- **lining:** 3D mesh for better ventilation | fast drying
- **tongue:** gusseted tongue with synthetic and water-resistant textile to keep dirt and liquid out of the shoe | loop to hold tongue in place
- **upper padding:** flexible and compact foam for better comfort and protection around malleolus and Achille's tendon zones.
- **toe cap:** metal-free | lighter than steel | conduct less heat and cold than a metal toe cap
- **penetration-resistant midsole :** metal-free | light and flexible | conducts less heat and cold than a metal sole | protects 100 % of the surface of the foot
- **insole:** removable | anatomically shaped with forefoot and heel shock absorbers | top layer in microfibre for better resistance to abrasion, very high moisture absorption capacity and fast drying | bottom layer of open cell foam with high shock absorption capacity and breathability | washable at 30°C
- French (EU) sizing system | width 11
- **weight:** 700 g in size 42