



# 739-8433 Data Sheet

ENGLISH

RS Stock number : 739-8433  
Type of tool : Air Body Saw  
Power source : Compressed air  
Maximum permissible operating pressure : 90 psi ( 6.2 bar )  
Recommended operating pressure : 90 psi ( 6.2 bar )

### Features

- High cutting performance
- Insulated handle and anti vibration cover
- 10mm maximum stroke with adjustable blade guide
- 1.2mm cutting capacity
- Safety throttle lever
- Well balanced
- Takes standard air body saw 12mm diameter flat end saw blades

### Specifications

- Material: Aluminium
- Size: 1.2mm Cutting Capacity
- Free Speed: 9,000RPM
- Weight: 0.9kgs / 2lbs
- Length: 11" / 279mm
- Min Hose Size: 3/8" / 10mm
- Air inlet thread: 1/4"
- Sound: 87dBA
- Vibration: 4m/s<sup>2</sup>
- Ave Air Consumption: 1cfm / 280 l/min
- Recommended lubrication: 10 Weight SAE Oil

# 739-8433

## Air Body Saw

## Technical Data



### Declaration of Conformity

We	RS Components Ltd
declare under our sole responsibility that the	739-8433– Air Body Saw
conforms with the directive and the standards	2006/42/EEC EN 792-6 ISO 28927